THE ALPHABOND REVIEW

www.alphabond.com.au

ISSUE 24

REVOLUTIONARY PRODUCTS FOR YOUR DENTAL NEEDS

~ CHROME EDITION ~



BRUSHA, BRUSHA, BRUSHA

Brushes perfect for chrome cobalt frames. Extremely durable and powerful, these slender brushes reach all the right places.



(*Top image*) 65mm diameter short 10mm x 12mm narrow. Featuring 2 rows of grade 1 Chungking bristles with an acrylic hub and wooden centre. (*Order code: R199-1000*) (*Middle image*) a slim, 44mm diameter, brush with an acrylic centre.



(Order code: R788-1000)

(Bottom image) Silver wire brush, doesn't remove surface, and gives a silky matte shine. 51mm diameter.

(Order code: R196-0000)





CAST-A-GEL HARRY!

Special reversible duplicating hydrocolloid for sophisticated partial dentures, combination work and the acrylic casting technique. High level impression accuracy, even with the finest of details. Tear-resistant due to its outstanding elasticity. This offers you the necessary reliability and precision in use.



Available in a 6kg bucket. (Order code: BG52052)

A robust duplicating unit, the Gelovit is an innovative preparation concept with temperature control which prevents clumping in the gel, and guarantees the quickest possible preparation without burning. Prevents deposits and blockage of the nozzles, and always gives a consistent homogeneity.

With a pre-programming feature, the Gelovit is the dependable process for optimum duplicating.

(Order code: BG26334)

AGAR DO, DO, DO

Looking for an environmentally friendly duplicating gel?

Wirogel's versatile agar-agar hydrocolloid investment will do! Univerally useful - this highly accurate impression investment



guarantees your highest demands are met. Five-times less expensive than silicone without compromising quality of precision. (Order code: BG54351)

LA-LA-LA

Wironit-LA Chrome Cobalt - A trusted and reliable alloy in the partial denture and combination technique. With low thermal conductivity it provides high-wearing patient comfort.



Specially developed for laser welding, it is also biocompatible and corrosion-resistant. Available in 1000g. (Order code: BG50100)









HARDER, BETTER, FASTER, STRONGER

Wironit-extra-hard is the ideal partial denture alloy. Its high elongation limit and tensile strength is perfectly suited for combination work. The special biocompatible and corrosionresistant composition with silicone and carbon gives outstanding casting properties. Very low thermal conductivity of the alloy also emphasises the wearing comfort of the prosthesis, and makes for a happier patient. Available in 1000g.

(Order code: BG50060)



For finishing and polishing chrome cobalt and hard metals, these hard classic black rubber cylinders are always ready for you. Available in a box of 100 pieces.

(Order code: DE4590)

Feel free to call us or check our website for the rest of our Dedeco product range!

YOU'LL BE JAMMIN' TO THIS MASTER BLASTER



The Triton SLA wet and dry steam environmentally cleaner is an sound, intensive and versatile unit. With a fixed water connection and interconnected demineralisation cartridge, it minimises calcification of the unit. Featuring 3 bar (approx.) steam pressure, it's gentle yet thorough. Corrosion resistant with an insulated spray gun for maximum comfort - you'll never want to clean with anything else!

(Order code: BG26005)



HARDEN UP PRINCESS

Bredent's 500ml investment hardener - Spray on and in 20 mins you'll have a scratchresistent model surface.

(Order code: BR55000004)

Korox® 250 sandblasting MR SANDMAN, SEND material is made from 99.6 % aluminium oxide ME SOME KOROX remains sharp-edged until it is completely worn. It not only removes investment material residues oxides efficiently, it's ideal for surface conditioning of alloys prior to ceramic firing. No risk contamination of the alloy surface too.

(Order code: BG46014 (8kg), BG54300 (20kg)



DIAMONDS ARE A LABS BEST FRIEND

So many sintered diamond tools - cutting discs, cones, barrels, wheels or bullets, whatever you need, we'll have it! For your cobalt chrome, non/semi-precious alloys, or ceramics. Here are a few, but call us or check our website for more!





THE ADAPTER

For quick and safe adapting of wax patterns in CoCr. Using the flat side, clasps can be perfectly placed and pressed on the investment model. Use the rounded side for stippled maxillary plates or retentions. Never damage or deform any wax pattern again!

(Order code: BR36001205)







www.alphabond.com.au Ph: (02) 9417 6660 E-mail: info@alphabond.com.au