

# WATER DISTILLER

It is extremely important that appropriate water is used in sterilisers. Using tap or tank water will void your autoclaves warranty as well as leading to a build up of scale in the chamber, valves and pipe-work, which in turn can lead to unwanted breakdowns.

- Mobile and easy to operate
- Automatic shutoff
- Strong and durable
- Easy to clean
- Produces 4 litres in 7 hour



Voltage Rating	AC220V,50~60Hz AC110V,60Hz
Power Rating	750W
Capacity	4L
Distiller Volume	1L/H
Temperature Over Safety	Power-off when temperature is 160°C
Net Weight	4kg